

DLG Test Report 6984

Trevos, a.s.

INNOVA ABS

Resistance to ammonia,
cleaning distance



**TREVOS
INNOVA ABS**
✓ Resistance to ammonia
✓ Cleaning distance
DLG Test Report 6984



TREVOS a.s. Hrabov 241 811 01 Turnov
TYP: INNOVA 140 W/8 PC 2000 840 116P
230V 50/60Hz 22W 10 80°C IP66 IP65
180021409 00 1050
CE

Overview

A test mark „DLG-APPROVED for individual criteria“ is awarded for agricultural products which have successfully fulfilled a scope-reduced usability testing conducted by DLG according to independent and recognized evaluation criteria. The test is intended to highlight particular innovations and key criteria of the test object. The test may contain criteria from the DLG test scope for overall tests, or focus on other value-determining characteristics and properties of the test subject. The minimum requirements, test conditions and procedures as well as the evaluation bases of the test results will be specified in consultation with an expert group of DLG. They correspond to the recognized rules of technology, as well as scientific and agricultural knowledge and requirements. The successful testing is concluded with the publication of a test report, as well as the awarding of the test mark which is valid for five years from the date of awarding.



The ammonia resistance test was performed as a laboratory test according to the patented DLG test standard. This test is intended to determine the suitability of equipment for animal living areas to withstand the impacts of animal environments. The cleaning distance test assesses the suitability for cleaning animal living areas. Other criteria were not tested. As of 2017 the luminaires will be operated in the test chamber both passively (without power supply) as well as actively according to a determined test program.

Assessment – Brief Summary

The LED light “INNOVA ABS” from Trevos, a.s. has successfully completed the DLG test for ammonia resistance and cleaning distance.

According to this result, it can be assumed that these luminaires are resistant to the typical environmental conditions of animal living areas and that no accelerated reduction of the product lifetime will occur.

Furthermore, the cleaning distance is regarded as suitable for the cleaning of animal houses. In addition, the LED light “INNOVA ABS” was operated actively in the chamber for the entirety of the test. No product damage was observed here.

Table 1:
Overview of results

Test result	Evaluation*
Resistance to ammonia of the luminaire housing	
resistant	+
Cleaning distance	
Minimum distance with flat spray nozzle: 10 cm	+
Ingress of water into the housing without damages: No	+

Evaluation scheme

Test result	Evaluation*
Resistance to ammonia	
resistant	+
partly resistant	○
non-resistant	-
Ingress of water into the housing without damages	
no/yes	+/-
Cleaning distance	
5 cm	++
10 cm	+
15 cm	○
20 cm	-
25 cm	--

* Evaluation range: ++ / + / ○ / - / -- (○ = standard, n.a. = not evaluated)

The Product

Manufacturer and applicant

Trevos, a.s.
Masov 34
51101 Turnov
Czech Republic

Product:
“INNOVA ABS/NB ABS/WB ABS”

Contact:
Phone +420 481 363 311
Telefax +420 481 624 681
trevos@trevos.cz
<https://trevos.eu/en/>

Description and technical data

The tested LED light “INNOVA ABS” is suitable for any usage in animal housing surroundings.

Table 2:
Technical data (according to manufacturer)

	INNOVA	
	1.4ft ABS/NB ABS/WB ABS	1.5ft ABS/NB ABS/WB ABS
Electrical connection		
Voltage	230 V	
Frequency	50-60 Hz	
Performance	18/22/30/43 W	22/27/37/54 W
Dimension and weight		
Length	1,175 mm	1,455 mm
Width	90 mm	
Height	93 mm	
Weight	1.5 kg	1.8 kg
Additional technical data		
Number of LED modules	1/2/3	
Housing material	diffuser: translucent AC, body: dark grey ABS	
Colour temperature	3000/4000/5000/6500 K	
Dimmable	yes, Dali (optional)	
Light angle	lambertian/narrow/wide beam	
Light yield	2340 ... 7170	

The Method

Resistance to ammonia

The ammonia resistance of the LED light “INNOVA ABS” was determined by a laboratory test with one luminaire according to the patented DLG test standard for agricultural use. The laboratory test is designed to replicate the conditions of a usage period of about 10 years exposure to animal living areas.

The test was carried out in a climate chamber under the following climate conditions:

Test duration	1500 h
Air temperature	70 °C
Relative humidity	70 %
Ammonia concentration	750 ppm

For assessing the ammonia resistance, each luminaire was examined visually, gravimetrically and the plastic parts additionally through measurement of the hardness (Shore D) before and after the climate testing. Since 2017, luminaires have additionally been following a cycle of operation predefined by DLG (3 hours on, 1 hour off) in order to evaluate any thermal impacts caused by switch-on and -off procedures during ammonia fumigation.

In order to avoid overheating (> 70 °C), the luminaires could be operated at a reduced power level during the testing period.

Cleaning distance

During test bench examinations of the mechanical resistance to high-pressure cleaners, the minimum cleaning distance was determined.

The minimum cleaning distance is defined as the distance between nozzle and surface when no damages can be observed at the housing surface.

The test was conducted under the conditions presented in table 3.

Table 3:

Test conditions cleaning distance

Line pressure	~150 bar
Water	cold, approx. 1,000 l/h, no detergents
Nozzle type	Flat spray nozzle, 25°
Exposition time	1 minute
Distance	250 mm, 200 mm, 150 mm, 100 mm, 50 mm
Ambient temperature	10 °C

For all test procedures, the LED light “INNOVA ABS” in length of 1,455 mm has been used. After the tests, the luminaires underwent visual examination to a reference sample that was identical in construction.

The Test Results in Detail

Resistance to ammonia

Visual test

The comparative visual examination after the ammonia exposure has shown minor discolorations at the luminaire housing.

During the test, the tube light appeared to be sufficiently gas-tight. Nevertheless it cannot be ruled out, that a limited amount of ammonium compounds could enter the luminaire housing. Again, no negative impact on the luminaire performance needs to be expected.

The defects are rated as insignificant. The examination of the manufacturer's mounting parts didn't also show any defects.

Gravimetric test

Weight comparisons before and after the ammonia fumigation have not shown any measurable increases or decreases in weight.

Hardness test

During the hardness test (Shore D) no measurable changes were observed. All determined changes were within the measurement uncertainty.

Functional test

No defects were observed. All luminaires worked after the conducted tests.

Based on the results of these tested parameters, the luminaire is evaluated as resistant to ammonia.

Cleaning distance

Even at a cleaning distance of only 100 mm, no damages to the luminaire could be observed.

At no time a water ingress into the luminaires was noticed.

In order to avoid damage to the luminaires during cleaning reliably, according to the manufacturer's specifications a minimum cleaning distance of 10 cm should always be ensured.

Summary

The results show that the LED light "INNOVA ABS" fulfills the testing requirements for ammonia resistance and cleaning distance (evaluation "○" or better) and thus receives the test mark DLG-Approved. It can be expected that the luminaire is resistant to ammoniacal air in animal living areas and that no accelerated reduction of the product lifetime occurs.

The LED light "INNOVA ABS" was operated both passively and actively during the ammonia fumigation in the test chamber and passed both tests successfully.

It is also recommended in any case to keep a minimum distance of 10 cm during cleaning.

Other criteria have not been assessed.

More information

Testing agency

DLG TestService GmbH, Gross-Umstadt location
The tests are conducted on behalf of DLG e.V.

DLG test framework

DLG-Approved Test "Ammonia resistance"
(current as of 07/2018)

Department

Agriculture

Division head

Dr. Ulrich Rubenschuh

Test engineer(s)

Dipl-Ing (FH) Tommy Pfeifer*

* Author

DLG – the open network and professional voice

Founded in 1885 by the German engineer Max Eyth, DLG (Deutsche Landwirtschafts-Gesellschaft – German Agricultural Society) is an expert organisation in the fields of agriculture, agribusiness and the food sector. Its mission is to promote progress through the transfer of knowledge, quality standards and technology. As such, DLG is an open network and acts as the professional voice of the agricultural, agribusiness and food sectors.

As one of the leading organisations in the agricultural and food market, DLG organises international trade fairs and events in the specialist areas of crop production, animal husbandry, machinery and equipment for farming and forestry work as well as energy supply and food technology. DLG's quality tests for food, agricultural equipment and farm inputs are highly acclaimed around the world.

For more than 130 years, our mission has also been to promote dialogue between academia, farmers and

the general public across disciplines and national borders. As an open and independent organisation, our network of experts collaborate with farmers, academics, consultants, policymakers and specialists in administration in the development of future-proof solutions for the challenges facing the agriculture and the food industry.

Leaders in the testing of agricultural equipment and input products

The DLG Test Center Technology and Farm Inputs and its test methods, test profiles and quality seals hold a leading position in testing and certifying equipment and inputs for the agricultural industry. Our test methods and test profiles are developed by an independent and impartial commission to simulate in-field applications of the products. All tests are carried out using state-of-the-art measuring and test methods applying also international standards.

Internal test code DLG: 19-125

Copyright DLG: © 2019 DLG



DLG TestService GmbH
Gross-Umstadt location

Max-Eyth-Weg 1 • 64823 Groß-Umstadt • Germany
Phone: +49 69 24788-600 • Fax: +49 69 24788-690
Tech@DLG.org • www.DLG.org

Download of all
DLG test reports free of charge
at: www.DLG-Test.de